

Wessington Cryogenics Ltd

2 Gadwall Road, Rainton Bridge South

Houghton-Le-Spring, Tyne & Wear, England DH4 5NL

Tel: +44 (0)191 512 0677 Email: info@wessingtoncryogenics.com




The CH BULK series of liquid helium dewars have been designed to meet the exacting requirements of ultra-low temperature applications in research and industry.

The larger capacity liquid helium vessels are commonly used in conjunction with liquefiers, or where the bulk storage of product is required. Vessels up to 20,000 litres are available.


Custom ladder location and instrument panel location can be supplied as an option.

	CH 1000	CH 2000	CH 3000	CH 4000	CH 5000	CH 6000	CH 7000	CH 10,000	CH 15,000	CH 20,000
Product Code	9917- 1000-0	9917- 2000-0	9917- 3000-0	9917- 4000-0	9917- 5000-0	9917- 6000-0	9917- 7000-0	9917- 10000-0	9917- 8500-0	9917- 20000-0
Capacity (litres)	1000	2000	3000	4000	5000	6000	7000	10,000	15,000	20,000
Diameter (mm)	1400	1700	1900	2000	2300	2300	2400	2650	3000	3300
Height (mm)*	1636	2003	2245	2599	2587	2838	2978	3408	3832	4092
Weight Empty (kg)	650	950	1150	1250	1350	1650	1750	1950	5000	7100
Weight Full (kg)	770	1200	1525	1690	1850	2275	2500	2825	6250	9600
Max Allowable Working	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
Pressure (bar G)										
Static Evaporation Rate (% per day)**	0.5	0.4	0.35	0.35	0.3	0.3	0.25	0.25	0.2	0.2
Neck Diameter Standard (mm)	100	140	160	160	160	160	200	200	305	305
	Code Capacity (litres) Diameter (mm) Height (mm)* Weight Empty (kg) Weight Full (kg) Max Allowable Working Pressure (bar G) Static Evaporation Rate (% per day)** Neck Diameter Standard	Product 29917-1000-0 Capacity (litres) 1000 Diameter (mm) 1400 Height 1636 Weight Empty (kg) 650 Weight Full (kg) 770 Max Allowable Working Pressure (bar G) Static Evaporation Rate (% per day)** Neck Diameter Standard	1000 2000 2000 2000 2000 2000-0 2000-0 2000-0 2000-0 2000-0 2000	Product Code	Product	Product Code				






VALVES/PIPEWORK



TYPICAL SIPHON GLAND ARRANGEMENT



TYPICAL SIPHON GLAND ARRANGEMENT					
1	Liquefier connection				
2	Transfer siphon				
3	Probe				

VALVES/ PIPEWORK (LIN, LOX, LAR)						
PG	Pressure gauge					
FM	Flow meter					
OSC1	Oscillation control damper					
OSC2	Oscillation control damper					
DP	Differential pressure transmitter					
RV1, RV2, RV3	Relief valve					
PRV1	Pressure regulating vent valve					
BD1, BD2, BD3	Burst disc					
NRV	Non return valve					
V1	Neck cooling valve					
V2	Flow meter control valve					
V3	Pressure gauge isolation					
V4	Gas feed to panel isolation valve					
V5	Manual gas use valve					
V6	Manual pressure regulating isolation valve					
V7	Divertor valve					
V8, V9	Bleed off valve					
V10	Differential pressure gauge equalising valve					
V11	Differential pressure gauge equalising valve (high pressure)					
V12	Differential pressure gauge equalising valve (low pressure)					
V13	Spare differential pressure gauge					
V14	equalising valve (high pressure) Spare differential pressure gauge equalising valve (low pressure)					
V15, V16, V17, V18	Optional isolation valve					
C1	Spare connection					
C2	KF25 half nipple					
C3	Spare connection					